

760255092 | PPL-SP-24LC-SM-PT-BEU-ANT



Propel Singlemode Splice Cassette, 24LC/UPC with internal shutters, 250 μm OS2 single fiber pigtailed, Method B Enhanced ULL, ANT Splice Protector

- Can be installed and removed from front or rear of panel
- This component requires 6 of the 12 lanes on the Propel Panel blade
- Compatible with either 250 μm or 900 μm incoming fiber

Recommended for use with 24f subunit cable

Product Classification

| | |
|------------------------------|-------------------------------|
| Regional Availability | Europe |
| Portfolio | SYSTIMAX® |
| Product Type | Fiber cassette with pigtailed |
| Product Brand | Propel |
| Product Series | PPL |

General Specifications

| | |
|-------------------------------|-------------------------|
| Color, front | Blue |
| Interface, front | LC/UPC |
| Interface, rear | Stranded pigtail |
| Polarity | Method B Enhanced (ULL) |
| Shuttered | Yes |
| Total Fibers, quantity | 24 |

Dimensions

| | |
|---------------|-----------------------|
| Height | 67.31 mm 2.65 in |
| Width | 196.012 mm 7.717 in |

Optical Specifications

| | |
|--------------------------------|------------|
| Fiber Mode | Singlemode |
| Fiber Type | G.657.A2 |
| Insertion Loss, maximum | 0.25 dB |

Environmental Specifications

Qualification Standards IEC 61753-1 | TIA-568.3-D
Safety Standard UL

Packaging and Weights

Included ANT holder | ANT mechanical splice protection
Packaging quantity 1

Regulatory Compliance/Certifications

| Agency | Classification |
|------------|-----------------------------------|
| CHINA-ROHS | Below maximum concentration value |
| ROHS | Compliant |
| UK-ROHS | Compliant |

