

# 760255093 | PPL-SP-24LC-OM4-PT-BEU-ANT



Propel Multimode Splice Cassette, 24LC with internal shutters, OM4 single fiber pigtailed, Method B Enhanced ULL, ANT Splice Protector

- Can be installed and removed from front or rear of panel
- This component requires 6 of the 12 lanes on the Propel Panel blade
- Compatible with either 250  $\mu\text{m}$  or 900  $\mu\text{m}$  incoming fiber

Recommended for use with 24f subunit cable

## Product Classification

<b>Regional Availability</b>	Europe
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Fiber cassette with pigtailed
<b>Product Brand</b>	Propel
<b>Product Series</b>	PPL

## General Specifications

<b>Color, front</b>	Aqua
<b>Interface, front</b>	LC/UPC
<b>Interface, rear</b>	Stranded pigtail
<b>Polarity</b>	Method B Enhanced (ULL)
<b>Shuttered</b>	Yes
<b>Total Fibers, quantity</b>	24

## Dimensions

<b>Height</b>	67.31 mm   2.65 in
<b>Width</b>	196.012 mm   7.717 in

## Optical Specifications

<b>Fiber Mode</b>	Multimode
<b>Fiber Type</b>	G.657.A2
<b>Insertion Loss, maximum</b>	0.15 dB

## Environmental Specifications

# 760255093 | PPL-SP-24LC-OM4-PT-BEU-ANT

---

**Qualification Standards** IEC 61753-1 | TIA-568.3-D

**Safety Standard** UL

## Packaging and Weights

**Included** ANT holder | ANT mechanical splice protection

**Packaging quantity** 1

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

