## UHGMXUCCN

**Base Product** 



Singlemode MPO12 APC (pinned) to Unconnectorized Fiber Trunk Cable Assembly, 192-Fiber, Armored Indoor Plenum

#### Product Classification

Regional Availability	Asia   Australia/New Zealand   China   Europe   India   Latin America   Middle East/Africa   North America	
Portfolio	CommScope®	
Product Type	Fiber trunk cable assembly	
Product Brand	Propel   SYSTIMAX ULL	
Ordering Note	For additional jacket colors, please contact a CommScope Sales Representative   For lengths greater than 999 ft (304 m), orders must be in meters   Minimum length may vary based on cable configuration	

#### General Specifications

I	
Connector A, quantity	16
Color, boot A	Black
Color, connector A	Green
Connector B, quantity	0
Construction Type	Armored   Stranded
Furcation Color	Yellow
Interface, Connector A	MPO-12/APC Male
Interface, Connector B	Unterminated
Jacket Color	Yellow
Polarity	Method B Enhanced (ULL)
Fibers per Subunit, quantity	12
Total Fibers, quantity	192
Dimensions	
Breakout Length	22 in
Cable Assembly Length Range (m)	3 - 305
Cable Assembly Length Range (ft)	10 - 999

Page 1 of 3

©2025 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: February 7, 2025



# UHGMXUCCN

### Ordering Tree

	BASE	CODE			·
Ja	icket Color		Breakout Length / Option		ength
	Yellow	В	metal gland		
		С	with pulling grip		
		z	36 inch extension with shelf mount, gland		
		Y	36 inch extension with shelf mount, gland, pulling grip		MOL
		J	23 inch breakout, with mounting clips	F	Feet
		к	23 inch breakout, with mounting clips, pulling grip both ends	М	Meter
		R	23 inch breakout, with 36 inch extension, mounting clips		
		s	23 inch breakout, with 36 inch extension mounting clips, pulling grip both ends		
		L	23 inch breakout, with 72 inch extension mounting clips		
		м	23 inch breakout, with 72 inch extension, mounting clips, pulling grip both ends		

### Mechanical Specifications

Cable Retention Strength, maximum	11.24 lb @ 0 °	I	4.40 lb @ 90 °

#### **Optical Specifications**

Fiber Mode	Singlemode
Fiber Type	G.657.A2, TeraSPEED®

#### **Environmental Specifications**

**Operating Temperature** 

-10 °C to +60 °C (+14 °F to +140 °F)

Environmental Space

Indoor | Plenum

### Regulatory Compliance/Certifications

Page 2 of 3

©2025 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: February 7, 2025

**COMMSCOPE**°

# UHGMXUCCN

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted
<b>50</b>	

#### Included Products

760256092 P-192-MZ-8G1-F12YL/20T	_	Fiber indoor cable, Plenum MPO Trunk, interlocking aluminum armored with plenum jacket, 192 fiber multi-unit with 12 fiber subunits, Singlemode G.657.A2/B2, Feet jacket marking, Yellow jacket color
860659010	-	MPO-12, ULTRA LOW LOSS, MALE, Singlemode, GREEN, 2mm

Page 3 of 3

©2025 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: February 7, 2025

