UHGQXUCTR

Base Product



Singlemode MPO8 APC (pinned) to Unconnectorized Fiber Trunk Cable Assembly, 16-Fiber, Armored Indoor Plenum

Product Classification

Regional Availability

Asia | Australia/New Zealand | China | Europe | India | Latin

America | Middle East/Africa | North America

Portfolio CommScope®

 Product Type
 Fiber trunk cable assembly

 Product Brand
 Propel | SYSTIMAX ULL

Ordering Note For additional jacket colors, please contact a CommScope Sales Representative | For

lengths greater than 999 ft (304 m), orders must be in meters | Minimum length may

vary based on cable configuration

General Specifications

Connector A, quantity 2

Color, boot A Gray

Color, connector A Green

Connector B, quantity 0

Construction Type Armored | Stranded

Furcation Color Yellow

Interface, Connector A MPO-08/APC Male

Interface, Connector B Unterminated

Jacket Color Yellow

Polarity Method B Enhanced (ULL)

Fibers per Subunit, quantity 8

Total Fibers, quantity 16

Dimensions

Breakout Length 22 in


Cable Assembly Length Range (m) 3 – 305

Cable Assembly Length Range (ft) 10 – 999

COMMSCOPE®

UHGQXUCTR

Ordering Tree



Mechanical Specifications

Cable Retention Strength, maximum $11.24 \text{ lb} @ 0 \degree | 4.40 \text{ lb} @ 90 \degree$

Optical Specifications

Fiber Mode Singlemode

Fiber Type G.657.A2, TeraSPEED®

Environmental Specifications

Operating Temperature $-10 \,^{\circ}\text{C}$ to $+60 \,^{\circ}\text{C}$ (+14 $^{\circ}\text{F}$ to +140 $^{\circ}\text{F}$)

Environmental Space Indoor | Plenum

Regulatory Compliance/Certifications

Agency	Classification
ANATEL	Compliant
CHINA-ROHS	Above maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted



COMMSCOPE®

UHGQXUCTR

Included Products

760256007 P-016-MZ-8G1-F08YL/20T Fiber indoor cable, Plenum MPO Trunk, interlocking aluminum armored with plenum jacket, 16 fiber with 8 fiber subunits, Gel-free, Singlemode G.657.A2/B2, Feet jacket marking, Yellow jacket color

860659022

– MPO-08, ULTRA LOW LOSS, MALE, Singlemode, GREEN, 2mm

