## UHVMXMXCG

**Base Product** 



#### Ultra Low Loss (ULL) OM5 MPO12 UPC (pinned) to MPO12 UPC (pinned) Fiber Trunk Cable Assembly, 36-Fiber, Armored Indoor Plenum

#### Product Classification

Regional Availability	Asia   Australia/New Zealand   China   Europe   India   Latin America   Middle East/Africa   North America
Portfolio	CommScope®
Product Type	Fiber trunk cable assembly
Product Brand	Propel   SYSTIMAX ULL
Ordering Note	For additional jacket colors, please contact a CommScope Sales Representative   For lengths greater than 999 ft (304 m), orders must be in meters   Minimum length may vary based on cable configuration

#### General Specifications

deneral specifications	
Connector A, quantity	3
Color, boot A	Black
Color, connector A	Lime green
Connector B, quantity	3
Color, boot B	Black
Color, connector B	Lime green
Construction Type	Armored   Stranded
Furcation Color	Lime green
Interface, Connector A	MPO-12/UPC Male
Interface, Connector B	MPO-12/UPC Male
Jacket Color	Lime green
Polarity	Method B Enhanced (ULL)
Fibers per Subunit, quantity	12
Total Fibers, quantity	36
Dimensions	
Breakout Length	22 in

Page 1 of 3


©2025 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: February 7, 2025



## UHVMXMXCG

Cable Assembly Length Range (m)	3 - 305
Cable Assembly Length Range (ft)	10 - 999

### Ordering Tree



#### Mechanical Specifications

Cable Retention Strength, maximum	11.24 lb @ 0 °   4.40 lb
Optical Specifications	
Fiber Mode	Multimode
Fiber Type	OM5, LazrSPEED®

### Environmental Specifications

**Operating Temperature** 

-10 °C to +60 °C (+14 °F to +140 °F)

@ 90°

Page 2 of 3

©2025 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: February 7, 2025



# UHVMXMXCG

**Environmental Space** 

Indoor | Plenum

### Regulatory Compliance/Certifications

Agency	Classification
ANATEL	Compliant
CHINA-ROHS	Above maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted



#### Included Products

760242131	
P-036-MZ-5G-F12LM/20T	

860659008

- Fiber indoor cable, LazrSPEED® Plenum MPO Trunk, interlocking aluminum armored with plenum jacket, Multimode OM5, 36 fiber multi-unit with 12 fiber subunits, Lime-green jacket color, Feet cable marking
- MP012, ULL, MALE, OM5, LIME, 2MM

Page 3 of 3

©2025 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: February 7, 2025

