


UKGMXMXCP



Singlemode MPO12 APC (pinned) to MPO12 APC (pinned)) Fiber Trunk Cable Assembly, 288-Fiber, Armored Indoor Dual Rated (OFNR/LSZH)

Product Classification

Regional Availability	Asia Australia/New Zealand China Europe India Latin America Middle East/Africa North America
Portfolio	CommScope®
Product Type	Fiber trunk cable assembly
Product Brand	Propel SYSTIMAX ULL
Ordering Note	For additional jacket colors, please contact a CommScope Sales Representative For lengths greater than 999 ft (304 m), orders must be in meters Minimum length may vary based on cable configuration

General Specifications

Connector A, quantity	24
Color, boot A	Black
Color, connector A	Green
Connector B, quantity	24
Color, boot B	Black
Color, connector B	Green
Construction Type	Armored Stranded
Furcation Color	Yellow
Interface, Connector A	MPO-12/APC Male
Interface, Connector B	MPO-12/APC Male
Jacket Color	Yellow
Polarity	Method B Enhanced (ULL)
Fibers per Subunit, quantity	12
Total Fibers, quantity	288


Dimensions

Breakout Length	22 in
Cable Assembly Length Range (m)	3 – 305

UKGMXXMXXCP

Cable Assembly Length Range (ft)10 – 999

Ordering Tree



Mechanical Specifications

Cable Retention Strength, maximum11.24 lb @ 0 ° | 4.40 lb @ 90 °

Optical Specifications

Fiber ModeSinglemode

Fiber TypeG.657.A2, TeraSPEED®

Environmental Specifications

Operating Temperature-10 °C to +60 °C (+14 °F to +140 °F)

EN50575 CPR Cable EuroClass Fire PerformanceDca

Environmental SpaceDual Rated LSZH/Riser | Indoor

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

UKGMXMXCP



Included Products

- | | | |
|---------------------------|---|---|
| 760256091 | – | Fiber indoor cable, Riser/LSZH rated MPO Trunk, interlocking aluminum armored, Singlemode |
| N-288-MZ-8G1-F12YL/20T/B2 | | G.657.A2/B2, 288 fiber, Feet jacket marking, Yellow jacket color, B2ca flame rating |
| 860659010 | – | MPO-12, ULTRA LOW LOSS, MALE, Singlemode, GREEN, 2mm |