MTC3752M3HDX



G2 Series High Capacity 3-Sector Monopole Frame, 12 ft 6 in 2.88 in OD face pipes, includes twelve 96 in 2.88 in OD antenna pipes plus six 96 in RRU pipes; For patents, see www.cs-pat.com.

OD

Product Classification

Product Type	High capacity monopole sector frame
Ordering Note	NSTD445 Compliant
General Specifications	
Mounting	Monopole, 381–1270 mm (15–50 in) 0
Pipe, quantity	18
Sectors, quantity	3
Dimensions	
Height	2,438.4 mm 96 in
Face Width	3.81 m 12.5 ft
Width	3,810 mm 150 in
Pipe Length	2,438.4 mm 96 in
Face Support Pipe Diameter	73.025 mm 2.875 in
Mounting Diameter, maximum	1270 mm 50 in
Mounting Diameter, minimum	304.8 mm 12 in
Pipe Outer Diameter	73.025 mm 2.875 in
Stand-off Distance	1,117.6 mm 44 in


Outline Drawing



©2025 ANDREW, an Amphenol company. All rights reserved. Amphenol and ANDREW are registered trademarks of Amphenol and/or its affiliates in the U.S. and other countries. All product names, trademarks and registered trademarks are property of their respective owners. Revised: March 12, 2025

Page 1 of 3

MTC3752M3HDX



PATENT PENDING

Material Specifications

Material Type

Hot dip galvanized steel

Mechanical Specifications

Wind Rating	For Specifications, please contact your local ANDREW representative
Wind Rating Test Method	TIA/EIA-222

Packaging and Weights

Included	Pipe mounts Plain end pipes (12) RRU Pipes (6) Ring mounts (2) Sector frames (3) Stiff arm
Packaging quantity	1
Weight, net	991.099 kg 2185 lb

Regulatory Compliance/Certifications

Classification

ISO 9001:2015

Agency

Designed, manufactured and/or distributed under this quality management system

* Footnotes

Wind Rating

BWS—Base Wind Speed; FBC—Florida Building Code

Page 2 of 3



Page 3 of 3



©2025 ANDREW, an Amphenol company. All rights reserved. Amphenol and ANDREW are registered trademarks of Amphenol and/or its affiliates in the U.S. and other countries. All product names, trademarks and registered trademarks are property of their respective owners. Revised: March 12, 2025