

UKVQZQZT8



Ultra Low Loss (ULL) OM5 MPO8 APC (pinned) to MPO8 APC (pinned)
Fiber Trunk Cable Assembly, 8-Fiber, Armored Indoor Dual Rated (OFNR
/LSZH)

Product Classification

Regional Availability	Asia Australia/New Zealand China Europe India Latin America Middle East/Africa North America
Portfolio	CommScope®
Product Type	Fiber trunk cable assembly
Product Brand	Propel SYSTIMAX ULL
Ordering Note	For additional jacket colors, please contact a CommScope Sales Representative For lengths greater than 999 ft (304 m), orders must be in meters Minimum length may vary based on cable configuration

General Specifications

Connector A, quantity	1
Color, boot A	Gray
Color, connector A	Green
Connector B, quantity	1
Color, boot B	Gray
Color, connector B	Green
Construction Type	Armored Stranded
Furcation Color	Lime green
Interface, Connector A	MPO-08/APC Male
Interface, Connector B	MPO-08/APC Male
Jacket Color	Lime green
Polarity	Method B Enhanced (ULL)
Fibers per Subunit, quantity	8
Total Fibers, quantity	8


Dimensions

Breakout Length	22 in
Cable Assembly Length Range (m)	3 – 305

UKVQZQZT8

Cable Assembly Length Range (ft) 10 – 999

Ordering Tree



Mechanical Specifications

Cable Retention Strength, maximum 11.24 lb @ 0 ° | 4.40 lb @ 90 °

Optical Specifications

Fiber Mode Multimode
Fiber Type OM5, LazrSPEED®

Environmental Specifications

Operating Temperature -10 °C to +60 °C (+14 °F to +140 °F)
EN50575 CPR Cable EuroClass Fire Performance Dca
Environmental Space Dual Rated LSZH/Riser | Indoor

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

UKVQZQZT8



Included Products

- | | | |
|--------------------------|---|---|
| 760256033 | – | Fiber indoor cable, Riser/LSZH rated, MPO Trunk, interlocking aluminum armored, Multimode |
| N-008-MZ-5G-F08LM/20T/B2 | | OM5, 8 fiber, Gel-free, Feet jacket marking, Lime green jacket color, B2ca flame rating |
| 860662230 | – | MPO8,ULL,Multimode,MALE,APC,GREEN,2 mm |