



Unshielded Discrete Distribution Module, M-series, (4 ea/pkg), Black

Product Classification

Regional Availability Asia | Australia/New Zealand | EMEA | Latin America | North America

Portfolio CommScope®

Product Type Module

General Specifications

Color Black

Dimensions

Height 43.434 mm | 1.71 in

Width 106.68 mm | 4.2 in

Depth 20.066 mm | 0.79 in

Material Specifications

Material Type High-impact, flame retardant, thermoplastic

Environmental Specifications

Operating Temperature -10 °C to +60 °C (+14 °F to +140 °F)

Storage Temperature -40 °C to +70 °C (-40 °F to +158 °F)

Relative Humidity Up to 95%, non-condensing

Flammability Rating UL 94 V-0

Safety Standard UL | cUL

Packaging and Weights

Packaging quantity 4

Weight, net 0.059 kg | 0.13 lb