# MC-KD12M-B



Heavy Duty Double T-Arm Monopole Mount Base Kit, Includes (2) Ring Mounts for 15"-50" OD Monopole, 12.5 ft x 3-1/2" OD face pipes. Antenna Pipes not included.

Heavy Duty Double T-Arm mount design for Monopole applications featuring sturdy corner tie-backs for added stability. Includes 3-1/2" OD face pipes. Antenna Pipes not included.

#### **Product Classification**

**Product Type** Monopole T-frame kit

#### General Specifications

**Mounting** Monopole, 381–1270 mm (15–50 in) OD

Pipe, quantity 0
Sectors, quantity 3

#### **Dimensions**

Face Width 3.81 m | 12.5 ft

Width 3,810 mm | 150 in

Mounting Diameter, maximum 1270 mm | 50 in

Mounting Diameter, minimum 381 mm | 15 in

Stand-off Distance 1,244.6 mm | 49 in

## Material Specifications

Material Type Hot dip galvanized steel

#### Mechanical Specifications

Wind Rating For Specifications, please contact your local ANDREW representative

Wind Rating Test Method TIA/EIA-222-G

### Packaging and Weights

Included Ring mounts (2) | Stand-off arms

Packaging quantity 1

**Weight, net** 725.367 kg | 1,599.16 lb

ANDREW® an Amphenol company

# MC-KD12M-B

## Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Above maximum concentration value

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted



## \* Footnotes

Wind Rating BWS—Base Wind Speed; FBC—Florida Building Code

