
## PM-SC2-B



Universal Open Face Pipe Mount Kit for 2-3/8 in OD pipe - Pipe Not Included.

Product Classification	
Product Type	Pipe mount
General Specifications	
Mounting	Angle 60°, 203.2 mm (8 in)   Angle 90°, 152.4 mm (6 in)   Straight or tapered legs up to 203.2 mm (8 in) OD
Note	One 96 in x 8 in panel antenna per sector
Pipe, quantity	0
Tower Taper	Non-tapered   Tapered
Dimensions	
Height	127 mm   5 in
Width	304.8 mm   12 in
Length	304.8 mm   12 in
Mounting Diameter, maximum	203.2 mm   8 in
Mounting Diameter, minimum	0 mm   0 in
Pipe Outer Diameter	60.96 mm   2.4 in
Stand-off Distance	203.2 mm   8 in
Material Specifications	
Material Type	Hot dip galvanized steel
Mechanical Specifications	
Wind Rating	120 mph (BWS) at 150 ft AGL
Wind Rating Test Method	TIA/EIA-222

### Packaging and Weights

Included

Sliding pipe mount brackets | Universal saddle mount

Page 1 of 2



# PM-SC2-B

#### Packaging quantity

Weight, net

47.6 kg | 104.94 lb

1

## Regulatory Compliance/Certifications

#### Agency

CHINA-ROHS

ISO 9001:2015

Classification Above maximum concentration value Designed, manufactured and/or distributed under this quality management system Compliant/Exempted Compliant/Exempted



ROHS

\* Footnotes

Wind Rating BWS-Base Wind Speed; FBC-Florida Building Code

ANDRE

n Amphenol company

©2025 ANDREW, an Amphenol company. All rights reserved. Amphenol and ANDREW are registered trademarks of Amphenol and/or its affiliates in the U.S. and other countries. All product names, trademarks and registered trademarks are property of their respective owners. Revised: March 12, 2025