

Non-Penetrating Roof Frame, 10 ft face, three 3-1/2 in OD x 96 in pipes

Product Classification

Product Type Non-penetrating roof frame

General Specifications

Mounting Non-penetrating

Pipe, quantity 3

Dimensions

 Height
 2,438.4 mm | 96 in

 Face Width
 3.2 m | 10.5 ft

Width 3,200.4 mm | 126 in

Length 2.53 m | 8.3 ft

 Pipe Length
 2,438.4 mm | 96 in

 Pipe Outer Diameter
 88.9 mm | 3.5 in

Material Specifications

Material Type Hot dip galvanized steel

Mechanical Specifications

Wind Rating For Specifications, please contact your local ANDREW representative

Wind Rating Test Method TIA/EIA-222

Packaging and Weights

Included Ballast tray | Frame | Pipe | Rubber mats, with or without pipe mounts

Packaging quantity 1

ANDREW® an Amphenol company

RF-NL10-DSH

Weight, net 333 kg | 734.138 lb

* Footnotes

Wind Rating BWS—Base Wind Speed; FBC—Florida Building Code

