

# SSC-760255777E1 | 15 in Pole Top for Ericsson 4455



## Top of Pole 15 in Dia Concealment Enclosure for Ericsson 4455 radio

- Orderable to mount multi-band and multi-port antennas from multiple antenna vendors
- Variable pole diameter mounting kits available to mount to existing structures
- Matching light pole or monopole options available

Pole Top Concealment that can accommodate most antenna manufacturers antennas. Please reach out to your ANDREW Representative for exact model number.

Mounts directly to ANDREW poles with no additional mounting materials. Mounts to other wood and metal poles with separately purchased mounts.

### Product Classification

Product Type	Pole top
Product Brand	Metro Cell
Ordering Note	ANDREW® standard product with terms
Warranty	One year

### General Specifications

Antenna Compatibility, ANDREW	ANDREW Canister Antennas
Antenna Compatibility, Other Vendors	ACE   AMPHENOL   DK   GALTRONICS   GAMMA NU   JMA   KATHREIN   KMW   ROSENBERGER
Antennas Included	None
Color Options	Antique Bronze (SRSL 45893)   Beige-Grey (RAL 7006)   Black (RAL 9005)   Black Green (RAL 6012)   Brown (RAL 8014)   Fairfax Brown (SW 2856)   Faux Concrete   Federal Park Brown   Green (RAL 6005)   Light Gray (RAL 7035)   Metallic Silver   Signal Black (RAL 9004)   White (RAL 9010)
Cooling	Passive Cooling
Mounting Options	Non-tapered poles   Tapered poles   Wood poles
Radio Compatibility, Ericsson	4455
Radios Included	None

### Dimensions

Height	1,066.8 mm   42 in
Width	381 mm   15 in
Depth	381 mm   15 in
Mounting Bolt Circle Diameter	142.748 mm   5.62 in   241.3 mm   9.5 in

# SSC-760255777E1 | 15 in Pole Top for Ericsson 4455

---

## Material Specifications

Finish Aluminum	Chromate
Finish Concealment Covers	Powder coated
Material Type	Aluminum   Steel

## Environmental Specifications

Thermal Compliance	GR-487
--------------------	--------

## Packaging and Weights

Weight (unloaded)	28.712 kg   63.3 lb
-------------------	---------------------