RF-NL10-3-96



Non-Penetrating Roof Frame, 10 ft face, three 3-1/2 in OD x 96 in pipes

Product Classification

Product Type

Non-penetrating roof frame

General Specifications

Mounting	Non-penetrating
Note	Four 96 in x 18 in panel antennas per sector
Pipe, quantity	3
Dimensions	
Height	2,438.4 mm 96 in
Face Width	3.2 m 10.5 ft
Width	3,200.4 mm 126 in
Length	2.53 m 8.3 ft
Pipe Length	2,438.4 mm 96 in
Pipe Outer Diameter	88.9 mm 3.5 in

Material Specifications

Material Type

Hot dip galvanized steel

Mechanical Specifications

 Wind Rating
 For Specifications, please contact your local ANDREW representative

 Wind Rating Test Method
 TIA/EIA-222

Packaging and Weights

Included

Rubber mats, with or without pipe mounts

Page 1 of 2



©2025 ANDREW, an Amphenol company. All rights reserved. Amphenol and ANDREW are registered trademarks of Amphenol and/or its affiliates in the U.S. and other countries. All product names, trademarks and registered trademarks are property of their respective owners. Revised: March 12, 2025

RF-NL10-3-96

Packaging quantity	1
Weight, net	309 kg 681.228 lb

* Footnotes

Wind Rating BWS–Base Wind Speed; FBC–Florida Building Code



©2025 ANDREW, an Amphenol company. All rights reserved. Amphenol and ANDREW are registered trademarks of Amphenol and/or its affiliates in the U.S. and other countries. All product names, trademarks and registered trademarks are property of their respective owners. Revised: March 12, 2025