

RF-NL10-4-96



Non-Penetrating Roof Frame, 10 ft face, Four 3-1/2 in OD x 96 in pipes

OBSOLETE

Product Classification

Product Type Non-penetrating roof frame

General Specifications

Mounting Non-penetrating

Note Four 96 in x 18 in panel antennas per sector

Pipe, quantity 4

Dimensions

Height 2,438.4 mm | 96 in

Face Width 3.2 m | 10.5 ft

Width 3,200.4 mm | 126 in

Length 2.53 m | 8.3 ft

Pipe Length 2,438.4 mm | 96 in

Pipe Outer Diameter 88.9 mm | 3.5 in

Material Specifications

Material Type Hot dip galvanized steel

Mechanical Specifications

Wind Rating For Specifications, please contact steelproducts@commscope.com or call 800-255-1479

Wind Rating Test Method TIA/EIA-222

RF-NL10-4-96

Packaging and Weights

Included	Rubber mats, with or without pipe mounts
Packaging quantity	1
Weight, net	309 kg 681.228 lb

* Footnotes

Wind Rating	BWS—Base Wind Speed; FBC—Florida Building Code
-------------	--