PPLA3X8LCQPL

Propel ULL Multimode OM4 Cabled Module, 12x8 duplex LC Propel module on End A to 1x8f MPO /UPC non-pinned on End B, 96 fiber B2ca Trunk, Method A

- This component requires 24 lanes on the Propel Panel blade
- Ultra-low loss (ULL) with Method A polarity
- End A module can be installed from rear of panel
- Serialized QR code provides easy access to factory optical test results

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

Portfolio SYSTIMAX®

Product Type Fiber cabled module

Product Brand Propel
Product Series PPL

Ordering Note For lengths greater than 999 ft (304 m), orders must be in meters | Maximum length is

400 meters

General Specifications

Configuration Type PROPEL Module to MPO Connector

Cable Color Aqua

Cable TypeTrunk Cable - LSZH Class B2ca

Interface, front LC/UPC

Interface Feature, front Duplex | Shuttered

Interface Color, front Aqua

Interface, rear MPO-08/UPC Female

Interface Feature, rear Key up/down | Unpinned

Module Size, end A8 fiberModule Size, end B8 fiberModule Quantity, end A12Module Quantity, end B12

Polarity Method A

Total Fibers, quantity 96

Total Ports, quantity, front 48



PPLA3X8LCQPL

Dimensions

 Height
 11 mm | 0.433 in


 Width
 65 mm | 2.559 in

 Depth
 170 mm | 6.693 in

Breakout Length, end B 12 in | 120 in | 33 in | 36 in | 48 in | 60 in | 72 in

Cable Assembly Length Range (m) 1 - 400 Cable Assembly Length Range (ft) 2 - 999

Ordering Tree



Optical Specifications

Fiber ModeMultimodeFiber TypeOM4Insertion Loss, maximum0.35 dB

Environmental Specifications

Qualification Standards IEC 61753-1 | TIA-568.3-D

Safety Standard c-UL-us

Packaging and Weights

Packaging quantity 1

COMMSC PE®

PPLA3X8LCQPL

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant



Included Products

760253123 N-096-MP-5K-F08AQ/20T/B2 Fiber indoor cable, LazrSPEED® Low Smoke Zero Halogen Riser MPO Trunk, 96 fiber with 2.0 mm Subunits, 96 fiber, Multimode OM4, Gel-free, Feet jacket marking, Aqua jacket color, B2ca flame rating