

RF-NL10-B

Non-Penetrating Roof Frame, 10 ft face, pipe not included



Product Classification

Product Type Non-penetrating roof frame

General Specifications

Mounting Non-penetrating

Note Four 96 in x 18 in panel antennas per sector

Pipe, quantity 0

Dimensions

Height 1905 mm | 75 in

Face Width 3.2 m | 10.5 ft

Width 3,200.4 mm | 126 in

Length 2.53 m | 8.3 ft

Pipe Length 0 mm | 0 in

Pipe Outer Diameter 88.9 mm | 3.5 in

Material Specifications

Material Type Hot dip galvanized steel

Mechanical Specifications

Wind Rating For Specifications, please contact your local ANDREW representative

Wind Rating Test Method TIA/EIA-222

Packaging and Weights

Included Rubber mats, with or without pipe mounts

RF-NL10-B

Packaging quantity	1
Weight, net	227 kg 500.449 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted



* Footnotes

Wind Rating	BWS—Base Wind Speed; FBC—Florida Building Code
-------------	--