

# RF-NL12-4-96

---



Non-Penetrating Roof Frame, 12 ft face, Four 3-1/2 in OD x 96 in pipes

## Product Classification

**Product Type** Non-penetrating roof frame

## General Specifications

**Mounting** Non-penetrating

**Note** Four 96 in x 18 in panel antennas per sector

**Pipe, quantity** 4

## Dimensions

**Height** 2,438.4 mm | 96 in

**Face Width** 3.81 m | 12.5 ft

**Width** 3,200.4 mm | 126 in

**Length** 2.53 m | 8.3 ft

**Pipe Length** 2,438.4 mm | 96 in

**Pipe Outer Diameter** 88.9 mm | 3.5 in

## Material Specifications

**Material Type** Hot dip galvanized steel

## Mechanical Specifications

**Wind Rating** For Specifications, please contact your local ANDREW representative

**Wind Rating Test Method** TIA/EIA-222

## Packaging and Weights

**Included** Rubber mats, with or without pipe mounts

# RF-NL12-4-96

---

Packaging quantity	1
Weight, net	374.1 kg   824.748 lb

\* Footnotes

Wind Rating	BWS—Base Wind Speed; FBC—Florida Building Code
-------------	--