Single Sector Chain Mount kit, 8 ft chain



Product Classification

Product Type Chain mount kit

General Specifications

Chains, quantity 2
Pipe, quantity 0
Sectors, quantity 1

Dimensions

 Height
 203.2 mm | 8 in

 Width
 203.2 mm | 8 in

 Length
 203.2 mm | 8 in

Chain Length 2,400.3 mm | 94.5 in

Mounting Diameter, maximum762 mm | 30 inMounting Diameter, minimum203.2 mm | 8 inPipe Outer Diameter60.96 mm | 2.4 inMounting Circumference, maximum2,392.68 mm | 94.2 in

Mounting Circumference, minimum 635 mm | 25 in

Material Specifications

Material Type Hot dip galvanized steel

Mechanical Specifications

Wind Rating 120 mph (BWS) at 100 ft AGL

Wind Rating Criteria One 96 in x 10 in panel antenna per sector

Wind Rating Test Method TIA/EIA-222

ANDREW® an Amphenol company

RR-CM130

Packaging and Weights

Included Brackets | Chains | Hardware

Packaging quantity

Weight, net 10 kg | 22.046 lb

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Above maximum concentration value

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted



* Footnotes

Wind Rating BWS—Base Wind Speed; FBC—Florida Building Code

