

RR-RM1560

Six Sector Ring Mount Kit



- Ring Mount for the attachment of radios and other equipment to the tower face.
- Designed to be a single connection point to the tower reducing costs associated with adding connection points to the tower.
- Allows for up to (6) mounting pipes.
- Accommodates 2-3/8" or 2-7/8" pipes
- Mast pipes & U-bolts ordered separate
- For 2-3/8" pipes use (2) "GUB-4240" per pipe
- For 2-7/8" pipes use (2) "GUB-4350" per pipe
- Pole range of 15" to 60" diameter

Product Classification

Portfolio	CommScope®
Product Type	Universal ring mount
Ordering Note	CommScope® standard product with terms
Warranty	One year

General Specifications

Mounting	Monopole, 381–1524 mm (15–60 in) OD
Pipe, quantity	0
Sectors, quantity	6

Dimensions

Height	254 mm 10 in
Length	152.4 mm 6 in
Mounting Diameter, maximum	1524 mm 60 in
Mounting Diameter, minimum	381 mm 15 in
Pipe Outer Diameter	0 mm 0 in
Mounting Circumference, maximum	4,785.36 mm 188.4 in

RR-RM1560

Mounting Circumference, minimum 1,196.34 mm | 47.1 in

Material Specifications

Material Type Hot dip galvanized steel

Packaging and Weights

Included Hardware | Mount

Packaging quantity 1

Weight, net 55.52 kg | 122.4 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant/Exempted
UK-ROHS	Compliant



* Footnotes

Warranty For more information, please consult our Product Warranty guidelines