RT-PM-B



Non-Penetrating Peak Roof Frame for 2 3/8 in to 4 1/2 in OD pipe, pipe not included

Product Classification

Product Type Non-penetrating roof frame

Warranty One year

General Specifications

Mounting Non-penetrating

Pipe, quantity 0

Dimensions

 Height
 965.2 mm | 38 in

 Width
 889 mm | 35 in

 Length
 1.219 m | 4 ft

Pipe Outer Diameter 114.3 mm | 4.5 in | 60.96 mm | 2.4 in | 73.66 mm | 2.9 in | 88.9 mm | 3.5 in

Material Specifications

Material Type Hot dip galvanized steel

Mechanical Specifications

Wind Rating Test Method TIA/EIA-222

Packaging and Weights

Included Hardware | Mount

Packaging quantity 1

Weight, net 47.6 kg | 104.94 lb

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Above maximum concentration value



RT-PM-B

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted



* Footnotes

Warranty For more information, please consult our Product Warranty guidelines

