

# RT-PM-B

---



Non-Penetrating Peak Roof Frame for 2 3/8 in to 4 1/2 in OD pipe, pipe not included

## Product Classification

<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Non-penetrating roof frame
<b>Warranty</b>	One year

## General Specifications

<b>Mounting</b>	Non-penetrating
<b>Pipe, quantity</b>	0

## Dimensions

<b>Height</b>	965.2 mm   38 in
<b>Width</b>	889 mm   35 in
<b>Length</b>	1.219 m   4 ft
<b>Pipe Outer Diameter</b>	114.3 mm   4.5 in   60.96 mm   2.4 in   73.66 mm   2.9 in   88.9 mm   3.5 in

## Material Specifications

<b>Material Type</b>	Hot dip galvanized steel
----------------------	--------------------------

## Mechanical Specifications

<b>Wind Rating Test Method</b>	TIA/EIA-222
--------------------------------	-------------

## Packaging and Weights

<b>Included</b>	Hardware   Mount
<b>Packaging quantity</b>	1
<b>Weight, net</b>	47.6 kg   104.94 lb

# RT-PM-B

---

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Above maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted



## \* Footnotes

<b>Warranty</b>	For more information, please consult our Product Warranty guidelines
-----------------	--