PPLU3G8LCQPL



Propel ULL Singlemode Cabled Module, 12x8 duplex LC Propel module on End A to 1x8f MPO/UPC non-pinned on End B, 96 fiber B2ca Trunk, Method B Enhanced

- This component requires 24 lanes on the Propel Panel blade
- Ultra-low loss (ULL) with Method B Enhanced polarity
- End A module can be installed from rear of panel
- Serialized QR code provides easy access to factory optical test results

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

Portfolio SYSTIMAX®

Product Type Fiber cabled module

Product Brand Propel
Product Series PPL

Ordering Note For lengths greater than 999 ft (304 m), orders must be in meters | Maximum length is

400 meters

General Specifications

Configuration Type PROPEL Module to MPO Connector

Cable Color Yellow

Cable Type Trunk Cable - LSZH Class B2ca

Interface, front LC/UPC

Interface Feature, front Duplex | Shuttered

Interface Color, front Blue

Interface, rear MPO-08/UPC Female

Interface Feature, rear Key up/up | Unpinned

Module Size, end A8 fiberModule Size, end B8 fiberModule Quantity, end A12Module Quantity, end B12

Polarity Method B Enhanced (ULL)

Total Fibers, quantity 96



PPLU3G8LCQPL

Total Ports, quantity, front 48

Dimensions

 Height
 11 mm | 0.433 in

 Width
 65 mm | 2.559 in

 Depth
 170 mm | 6.693 in

Breakout Length, end B 12 in | 120 in | 33 in | 36 in | 48 in | 60 in | 72 in

Cable Assembly Length Range (m) 1 - 400 Cable Assembly Length Range (ft) 2 - 999

Ordering Tree



Optical Specifications

Fiber Mode Singlemode

Fiber Type OS2
Insertion Loss, maximum 0.6 dB

Environmental Specifications

Qualification Standards IEC 61753-1 | TIA-568.3-D

Safety Standard c-UL-us

Packaging and Weights

COMMSCOPE®

PPLU3G8LCQPL

Packaging quantity

1

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Above maximum concentration value

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted



Included Products

760254320 – Fiber indoor cable, Low Smoke Zero Halogen Riser MPO Trunk, 96 fiber with 2.0 mm Subunits, N-096-MP-8G1-F08YL/20T/B2 Singlemode G.657.A2/B2, Feet jacket marking, Yellow jacket color, B2ca flame rating

