

SA-ISO



PIM-Guard®, PIM-free, isolator snaps in between hanger and mounting surface, and between stacked hangers to remove metal to metal contact

Product Classification

Product Type	Adapter
Product Brand	PIM-Guard®
Ordering Note	CommScope® standard product (Global)

General Specifications

Accessories	Adapters
Color	Black
Hanger Type	Snap-in hanger
Mounting	3/4 in drilled cable ladder 3/4 in through hole

Dimensions

Height	26.9 mm 1.059 in
Width	43.94 mm 1.73 in
Length	3.56 mm 0.14 in

Electrical Specifications

Return Loss Effect, maximum	0.1 dB
DTF Effect, maximum	0.1 dB

Material Specifications

Material Type	Engineered plastic
----------------------	--------------------

Mechanical Specifications

Maximum Loading	Double stack for hangers SSH-M, SSH-L, SSH-XL Double stack, 1-5/8 in cable Triple stack, 1/2 in cable
Vibration Survival	≥4 hours at resonant frequency

SA-ISO

Environmental Specifications

Operating Temperature	-40 °C to +85 °C (-40 °F to +185 °F)
Environmental Strength Capability	Double cable weight
UV Resistance, minimum with no degradation	≥1000 hours exposure in accelerated UV life chamber

Packaging and Weights

Height, packed	17 cm 6.693 in
Width, packed	13 cm 5.118 in
Length, packed	10 cm 3.937 in
Packaging quantity	10
Weight, gross	0.15 kg 0.331 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

