

# SF-HPM35-126

---



Heavy Duty Square T-Arm Base Kit with two 10 ft 6 in, 3-1/2 in OD face pipe supports, includes pipe

## Product Classification

**Product Type** Co-location dual pipe mount kit

## General Specifications

**Mounting** Angle 60°, 203.2 mm (8 in) | Angle 90°, 152.4 mm (6 in) | Straight or tapered legs up to 203.2 mm (8 in) OD

**Pipe, quantity** 2

**Tower Taper** Non-tapered | Tapered

## Dimensions

**Height** 3,200.4 mm | 126 in

**Face Width** 0.152 m | 0.5 ft

**Width** 1,676.4 mm | 66 in

**Length** 609.6 mm | 24 in

**Pipe Length** 3,200.4 mm | 126 in

**Mounting Diameter, maximum** 203.2 mm | 8 in

**Mounting Diameter, minimum** 0 mm | 0 in

**Pipe Outer Diameter** 88.9 mm | 3.5 in

**Stand-off Distance** 508 mm | 20 in

## Material Specifications

**Material Type** Hot dip galvanized steel

## Mechanical Specifications

**Wind Rating** 120 mph (BWS) at 100 ft AGL

**Wind Rating Test Method** TIA/EIA-222

# SF-HPM35-126

---

## Packaging and Weights

<b>Included</b>	Clamps   Frame   Pipe mounts   Pipes   Saddle mounts
<b>Packaging quantity</b>	1
<b>Weight, net</b>	156.988 kg   346.1 lb

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Above maximum concentration value
ROHS	Compliant/Exempted
UK-ROHS	Compliant



## \* Footnotes

<b>Wind Rating</b>	BWS—Base Wind Speed; FBC—Florida Building Code
--------------------	--