

# MC-S10M-12-96



Monopole Co-location Square Tube T-Frame kit for 15 in to 50 in OD Monopoles, 10 ft face, includes (12) 2-3/8" x 96" pipes

## Product Classification

**Product Type** Monopole T-frame kit

## General Specifications

**Mounting** Monopole, 381–1270 mm (15–50 in) OD  
**Pipe, quantity** 12  
**Sectors, quantity** 3

## Dimensions

**Height** 2,438.4 mm | 96 in  
**Face Width** 3.048 m | 10 ft  
**Width** 3,048 mm | 120 in  
**Pipe Length** 2,438.4 mm | 96 in  
**Mounting Diameter, maximum** 1270 mm | 50 in  
**Mounting Diameter, minimum** 381 mm | 15 in  
**Pipe Outer Diameter** 60.96 mm | 2.4 in  
**Stand-off Distance** 914.4 mm | 36 in

## Material Specifications

**Material Type** Hot dip galvanized steel

## Mechanical Specifications

**Wind Rating Test Method** TIA/EIA-222-G

## Packaging and Weights

**Included** Pipe mounts | Plain end pipes (12) | Ring mount | Square support rail | Stand-off arms  
**Packaging quantity** 1  
**Weight, net** 582.685 kg | 1,284.6 lb

