

STS3-12

Three-way Snap-in Stand-off Adapter kit for 1–2 in round members



Product Classification

| | |
|----------------------|------------------------------|
| Product Type | Adapter |
| Product Brand | HELIAX® |
| Ordering Note | ANDREW® non-standard product |

General Specifications

| | |
|---------------------|------------------------------------|
| Adapter Type | Stand-off adapter |
| Mounting | 3/4 in through hole Round member |

Dimensions

| | |
|-------------------------------------|-------------------------|
| Outside Width | 1,012.444 mm 39.86 in |
| Outside Length | 1,975.104 mm 77.76 in |
| Compatible Diameter, maximum | 50.8 mm 2 in |
| Compatible Diameter, minimum | 25.4 mm 1 in |
| Material Thickness | 2.591 mm 0.102 in |

Material Specifications

| | |
|----------------------|-----------------|
| Material Type | Stainless steel |
|----------------------|-----------------|

Mechanical Specifications

| | |
|------------------------|------------------------------|
| Maximum Loading | Double stack, 1-5/8 in cable |
|------------------------|------------------------------|

Packaging and Weights

| | |
|-----------------------|------------------|
| Height, packed | 12 cm 4.724 in |
| Width, packed | 11 cm 4.331 in |

STS3-12

| | |
|---------------------------|--------------------|
| Length, packed | 1 cm 0.394 in |
| Packaging quantity | 10 |
| Weight, gross | 0.58 kg 1.279 lb |

Regulatory Compliance/Certifications

| Agency | Classification |
|---------------|--|
| CHINA-ROHS | Below maximum concentration value |
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system |
| REACH-SVHC | Compliant as per SVHC revision on www.andrew.com/ProductCompliance |
| ROHS | Compliant |
| UK-ROHS | Compliant |



Included Products

| | |
|---------|--|
| 31670-1 | - Round Member Adapter for 1–2 in round members |
| SA-38 | - Three-Way Snap-in Stand-off Adapter has two slots for round member attachment and 3/8" holes for angle adapter integration. It includes three 3/4" holes for Snap-in hangers |

31670-1



Round Member Adapter for 1–2 in round members

Product Classification

| | |
|----------------------|-----------------------------------|
| Product Type | Adapter |
| Ordering Note | ANDREW® standard product (Global) |

General Specifications

| | |
|---------------------|----------------------|
| Adapter Type | Round member adapter |
|---------------------|----------------------|

Dimensions

| | |
|-------------------------------------|---------------------|
| Compatible Diameter, maximum | 50.8 mm 2 in |
| Compatible Diameter, minimum | 25.4 mm 1 in |
| Material Thickness | 0.711 mm 0.028 in |

Material Specifications

| | |
|----------------------|-----------------|
| Material Type | Stainless steel |
|----------------------|-----------------|

Mechanical Specifications

| | |
|-------------------------------------|------------------------------|
| Installation Torque, maximum | 6.6 ft lb 8.948 N-m |
| Installation Torque, minimum | 4.1 ft lb 5.559 N-m |
| Maximum Loading | Triple stack, 1-5/8 in cable |

Packaging and Weights

| | |
|---------------------------|--------------------|
| Height, packed | 15 cm 5.906 in |
| Width, packed | 10 cm 3.937 in |
| Length, packed | 10 cm 3.937 in |
| Packaging quantity | 10 |
| Weight, gross | 0.23 kg 0.507 lb |

Regulatory Compliance/Certifications

31670-1

Agency

CHINA-ROHS
ISO 9001:2015
REACH-SVHC
ROHS
UK-ROHS

Classification

Below maximum concentration value
Designed, manufactured and/or distributed under this quality management system
Compliant as per SVHC revision on www.andrew.com/ProductCompliance
Compliant
Compliant



SA-38



Three-Way Snap-in Stand-off Adapter has two slots for round member attachment and 3/8" holes for angle adapter integration. It includes three 3/4" holes for Snap-in hangers

Product Classification

| | |
|----------------------|-----------------------------------|
| Product Type | Adapter |
| Product Brand | HELIAX® |
| Ordering Note | ANDREW® standard product (Global) |

General Specifications

| | |
|---------------------|--|
| Adapter Type | Stand-off adapter |
| Mounting | 3/4 in through hole 3/8 in through hole Round member |

Dimensions

| | |
|---------------------------|---------------------|
| Height | 2.54 mm 0.1 in |
| Outside Width | 41.402 mm 1.63 in |
| Outside Length | 85.852 mm 3.38 in |
| Material Thickness | 2.591 mm 0.102 in |

Material Specifications

| | |
|----------------------|-----------------|
| Material Type | Stainless steel |
|----------------------|-----------------|

Mechanical Specifications

| | |
|------------------------|------------------------------|
| Maximum Loading | Double stack, 1-5/8 in cable |
|------------------------|------------------------------|

Packaging and Weights

| | |
|---------------------------|------------------|
| Height, packed | 12 cm 4.724 in |
| Width, packed | 11 cm 4.331 in |
| Length, packed | 1 cm 0.394 in |
| Packaging quantity | 10 |

SA-38

Weight, gross 0.58 kg | 1.279 lb

Regulatory Compliance/Certifications

| Agency | Classification |
|---------------|--|
| CHINA-ROHS | Below maximum concentration value |
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system |
| REACH-SVHC | Compliant as per SVHC revision on www.andrew.com/ProductCompliance |
| ROHS | Compliant |
| UK-ROHS | Compliant |

