



any pigtails and/or adapters are not shown in the image



HFTP-AM Customer premises fiber wall outlet, two pigtails, one Duplex LC/UPC adapter with inner shutters

- Compact fiber wall outlet for use at the final fiber termination point in the customer premises
- Can be wall mounted and mounted on wall boxes with fixation points of 60mm
- Direct termination with field installable connectors
- Laser safe with in-built individual shutters

Product Classification

| | |
|-------------------------------|-------------------|
| Product Type | Fiber wall outlet |
| Product Series | HFTP |
| Minimum Order Quantity | 75 |

General Specifications

| | |
|------------------------------------|------------|
| Color | White |
| Cover Type | Screw-on |
| Interface Type | LC/UPC |
| Mounting | Wall mount |
| Pigtails Included, quantity | 0 |
| Total Ports, quantity | 1 |

Dimensions

| | |
|---------------|----------------------|
| Height | 104.902 mm 4.13 in |
| Width | 84.836 mm 3.34 in |
| Depth | 24.892 mm 0.98 in |

Material Specifications

| | |
|----------------------|--------------------|
| Material Type | LSZH thermoplastic |
|----------------------|--------------------|

Optical Specifications

| | |
|-------------------|------------|
| Fiber Mode | Singlemode |
|-------------------|------------|

Environmental Specifications

| | |
|----------------------------|--------------------------------------|
| Storage Temperature | -30 °C to +60 °C (-22 °F to +140 °F) |
|----------------------------|--------------------------------------|

760256169 | HFTP-AM-L121-E

Relative Humidity Up to 93%, non-condensing

Environmental Space Indoor

Packaging and Weights

Packaging quantity 75