FD3-AC096J00JJBP1



FDH 3000 Fiber Distribution Extra Small Cabinet, 96 Fiber, SC/APC, no splitters, dielectric loose tube, 100 ft, 12FF

Product Classification

Regional Availability North America

Product Type Fiber distribution hub

Product Series FDH 3000

General Specifications

Access Front

Cable TypeDielectric - Loose Tube

Color Putty white

Distribution Cables, quantity 1

Distribution Ports, quantity 96

Fibers per Distribution Cable, quantity 96

Fibers per Feeder Cable, quantity 12

Interface, Input SC

Interface Feature, Input APC

Mounting Pad

Splitter Slots, quantity 9

Dimensions

 Height
 914.4 mm | 36 in

 Width
 533.4 mm | 21 in

 Depth
 355.6 mm | 14 in

 Cable Length
 30.48 m | 100 ft

Enclosure Size Extra small

Material Specifications

Finish Powder coated

Material Type Aluminum

COMMSCOPE®

FD3-AC096J00JJBP1

Environmental Specifications

Environmental Space Above ground

Packaging and Weights

Packaging quantity

Packaging Type Pallet

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Above maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted

