## FD3-AC144J00GBBP4



FDH 3000 Fiber Distribution Extra Small Cabinet, 144F, SC/APC, no splitters, Single armor loose tube, 100 ft, 48FF

#### **Product Classification**

Regional Availability North America

**Product Type** Fiber distribution hub

Product Series FDH 3000

General Specifications

**Access** Front

Cable TypeDielectric - Loose Tube

**Color** Putty white

**Distribution Cables, quantity** 

**Distribution Ports, quantity** 144

Fibers per Distribution Cable, quantity 144

Fibers per Feeder Cable, quantity 48

Interface, Input SC

Interface Feature, Input APC

**Mounting** Pad

Splitter Slots, quantity 9

#### Dimensions

 Height
 914.4 mm | 36 in

 Width
 533.4 mm | 21 in

 Depth
 355.6 mm | 14 in

 Cable Length
 30.48 m | 100 ft

**Enclosure Size** Extra small

Material Specifications

**Finish** Powder coated

Material Type Aluminum

**COMMSCOPE®** 

# FD3-AC144J00GBBP4

### **Environmental Specifications**

Environmental Space Above ground

Packaging and Weights

Packaging quantity

Packaging Type Pallet

## Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Above maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted

