## TF-ML3S2-20



Tower Face Mount with dual 20 ft x 3-1/2 in OD face pipe supports, includes pipe

## **Product Classification**

**Product Type** Tower face mount

General Specifications

Mounting Angle 60°, 203.2 mm (8 in) | Angle 90°, 152.4 mm (6 in) | Straight or tapered legs up to 203.2

mm (8 in) OD

Pipe, quantity

Tower Taper Non-tapered | Tapered

**Dimensions** 

**Height** 1,600.2 mm | 63 in

**Face Width** 6.096 m | 20 ft

**Width** 6,096 mm | 240 in

**Length** 304.8 mm | 12 in

**Pipe Length** 1,600.2 mm | 63 in

Face Support Pipe Diameter 88.9 mm | 3.5 in

Mounting Diameter, maximum 203.2 mm | 8 in

**Mounting Diameter, minimum** 0 mm | 0 in

Pipe Outer Diameter 114.3 mm | 4.5 in

Material Specifications

Material Type Hot dip galvanized steel

Mechanical Specifications

Wind Rating 120 mph (BWS) at 100 ft AGL

Wind Rating Test Method TIA/EIA-222

Packaging and Weights



## TF-ML3S2-20

Included Crossover plates | Pipes | Saddle mounts

Packaging quantity 1

**Weight, net** 313.478 kg | 691.1 lb

\* Footnotes

Wind Rating BWS—Base Wind Speed; FBC—Florida Building Code

