


FD3-AE288J00JBDP2P



FDH 3000 Fiber Distribution Small Cabinet, 288F, SC/APC, no splitters, dielectric loose tube, 200 ft, 24FF

Product Classification

Regional Availability	North America
Product Type	Fiber distribution hub
Product Series	FDH 3000

General Specifications

Access	Front
Cable Type	Dielectric - Loose Tube
Color	Putty white
Distribution Cables, quantity	1
Distribution Ports, quantity	288
Fibers per Distribution Cable, quantity	144
Fibers per Feeder Cable, quantity	24
Interface, Input	SC
Interface Feature, Input	APC
Mounting	Pole
Splitter Slots, quantity	9

Dimensions

Height	914.4 mm 36 in
Width	533.4 mm 21 in
Depth	355.6 mm 14 in
Cable Length	60.96 m 200 ft
Enclosure Size	Small

Material Specifications

Finish	Powder coated
Material Type	Steel

FD3-AE288J00JBDP2P

Environmental Specifications

Environmental Space Above ground

Packaging and Weights

Packaging quantity 1

Packaging Type Pallet

Regulatory Compliance/Certifications

Agency

Classification

CHINA-ROHS

Above maximum concentration value

REACH-SVHC

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS

Compliant/Exempted

UK-ROHS

Compliant/Exempted

