FD3-MM288J00M0MF0C



Indoor FDH 3000 w/ 288f Shell, 288f distribution loaded, no splitters included, MPO distribution connectors, and a 48f Feeder using Spliced Ribbon Pigtails

Indoor FDH 3000 w/ 288f Shell, 288f distribution loaded, no splitters included, MPO distribution connectors, and a 48f Feeder using Spliced Ribbon Pigtails

Product Classification

Regional Availability North America

Product Type Fiber distribution hub

Product Series IFDH 3000

General Specifications

Functionality Patching | Splicing

Access Front
Adapters, quantity 288

Color Putty white

Distribution Cables, quantity 24
Fibers per Distribution Cable, quantity 12
Fibers per Feeder Cable, quantity 48

Front Door Type Single hinged

InterfaceSC/APCMountingWallPort, quantity288Splitter Slots, quantity18

Dimensions

 Height
 839 mm | 33.032 in

 Width
 600 mm | 23.622 in

 Depth
 427 mm | 16.811 in

Enclosure Size Medium

Material Specifications

COMMSCOPE®

FD3-MM288J00M0MF0C

Finish Powder coated

Material Type Aluminum

Optical Specifications

Fiber Mode Singlemode

Environmental Specifications

Environmental Space Indoor

Packaging and Weights

Packaging quantity

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Above maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted

