MP-PP13M-12C-96



PIM Optimized Adjustable Monopole Platform with 13ft Face - 2-7/8in OD Face Pipes & Top Rail - Includes (12) 2-7/8in OD x 96in Antenna Pipes

Product Classification

Product Type Co-location platform

Product Brand PIM-guard

General Specifications

Monopole, 304.8–1143 mm (12–45 in) OD

Pipe, quantity 12
Sectors, quantity 3

Dimensions

Height 2,438.4 mm | 96 in

Face Width 3.962 m | 13 ft

 Width
 3,962.4 mm | 156 in

 Pipe Length
 2,438.4 mm | 96 in

Face Support Pipe Diameter 73.152 mm | 2.88 in

Mounting Diameter, maximum1,143 mm | 45 inMounting Diameter, minimum304.8 mm | 12 inPipe Outer Diameter73.152 mm | 2.88 in

Material Specifications

Material Type Hot dip galvanized steel

Mechanical Specifications

Wind Rating Test Method TIA/EIA-222

Packaging and Weights

Included Plain end pipes (12) | Platform | Rail | Ring mount

Packaging quantity 1

MP-PP13M-12C-96

Weight, net

1,134.389 kg | 2,500.9 lb

