# MP-PP15M-12C-126



PIM Optimized Adjustable Monopole Platform with 15ft Face - 2-7/8in OD Face Pipes & Top Rail - Includes (12) 2-7/8in OD x 126in Antenna Pipes

#### **Product Classification**

**Product Type** Co-location platform

Product Brand PIM-guard

#### General Specifications

**Monopole**, 304.8–1143 mm (12–45 in) OD

Pipe, quantity 12
Sectors, quantity 3

#### **Dimensions**

**Height** 3,200.4 mm | 126 in

**Face Width** 4.572 m | 15 ft

 Width
 4,572 mm | 180 in

 Pipe Length
 3,200.4 mm | 126 in

**Face Support Pipe Diameter** 73.152 mm | 2.88 in

Mounting Diameter, maximum1,143 mm | 45 inMounting Diameter, minimum304.8 mm | 12 inPipe Outer Diameter73.152 mm | 2.88 in

## Material Specifications

Material Type Hot dip galvanized steel

## Mechanical Specifications

Wind Rating Test Method TIA/EIA-222

#### Packaging and Weights

Included Plain end pipes (12) | Platform | Rail | Ring mount

Packaging quantity 1

ANDREW® an Amphenol company

# MP-PP15M-12C-126

Weight, net

1,358.146 kg | 2,994.2 lb

