MP-PP15M-15C-126



PIM Optimized Adjustable Monopole Platform with 15ft Face - 2-7/8in OD Face Pipes & Top Rail - Includes (15) 2-7/8in OD x 126in Antenna Pipes

Product Classification

Product Type Co-location platform

Product Brand PIM-guard

General Specifications

Monopole, 304.8–1143 mm (12–45 in) OD

Pipe, quantity 15
Sectors, quantity 3

Dimensions

Height 3,200.4 mm | 126 in

Face Width 4.572 m | 15 ft

 Width
 4,572 mm | 180 in

 Pipe Length
 3,200.4 mm | 126 in

Face Support Pipe Diameter 73.152 mm | 2.88 in

Mounting Diameter, maximum1,143 mm | 45 inMounting Diameter, minimum304.8 mm | 12 inPipe Outer Diameter73.152 mm | 2.88 in

Material Specifications

Material Type Hot dip galvanized steel

Mechanical Specifications

Wind Rating Test Method TIA/EIA-222

Packaging and Weights

Included Plain end pipes | Platform | Rail | Ring mount

Packaging quantity 1

ANDREW® an Amphenol company

MP-PP15M-15C-126

Weight, net

1,463.969 kg | 3,227.5 lb

