

# FD3-PA096J00U4210



FDH 3000 Fiber Distribution Hub in a Pedestal, 96F, SC/APC, no splitters, stranded pigtails, 96 splice cap, 4 splice trays, 6F spliced feeder

- Metal cabinet and can be placed in the ground without pouring a concrete pad or installing a hand hole
- Typically deployed for neighborhoods of 144 homes or higher
- Features full size trays for splicing incoming feeder and outgoing distribution cables and the option of adding hardened drop connections
- Modeled after the FDH 3000 fiber distribution hubs

## Product Classification

<b>Regional Availability</b>	North America
<b>Product Type</b>	Hub in a pedestal
<b>Product Series</b>	FDH 3000

## General Specifications

<b>Access</b>	Front   Rear
<b>Cable Type</b>	Pigtails - Stranded
<b>Color</b>	Green
<b>Distribution Ports, quantity</b>	96
<b>Fibers per Feeder Cable, quantity</b>	6
<b>Interface, Input</b>	SC
<b>Interface Feature, Input</b>	APC
<b>Mounting</b>	Pedestal
<b>Splice Tray Included, quantity</b>	4
<b>Splice Tray Type Included</b>	24-way, heat shrink
<b>Splicing Capacity, maximum</b>	96
<b>Splitter Slots, quantity</b>	6

## Dimensions

<b>Height</b>	889 mm   35 in
<b>Width</b>	292.1 mm   11.5 in
<b>Depth</b>	368.3 mm   14.5 in
<b>Enclosure Size</b>	Small

# FD3-PA096J00U4210

---

## Material Specifications

**Material Type** Molded plastic

## Environmental Specifications

**Environmental Space** Above ground

## Packaging and Weights

**Included** Cable clamps (2)

**Packaging quantity** 1

**Packaging Type** Pallet

## Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

