

FGSB-MHIS-B/H



FiberGuide® 6in Cut-in T for 4x18 and 4x24in, Black

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Tee
Product Brand	FiberGuide®
Product Series	FGS

General Specifications

Product Feature	Transition
Color	Black
Orientation	Horizontal
Section Type	Tee section

Dimensions

Width	152 mm 5.984 in
Length	396 mm 15.591 in
System Dimensions	102 mm x 152 mm (4 in x 6 in) 102 mm x 457 mm (4 in x 18 in) 102 mm x 610 mm (4 in x 24 in)

Material Specifications

Material Type	Engineering Thermoplastic
---------------	---------------------------

Environmental Specifications

Flammability Rating	CSA S143 UL 2024 UL 94 V-0
Halogen Characteristics	Blue Angel TCO '99 WEEE
Safety Standard	CSA UL

Packaging and Weights

FGSB-MHIS-B/H

Weight, net 0.98 kg | 2.161 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

