# TTS3-56



Three-way Stand-off Adapter Kit for 5–6 in round members, includes UAAI insert

#### **Product Classification**

**Product Type** Stand-off mount

Product Brand HELIAX®

Ordering Note ANDREW® non-standard product

#### General Specifications

Adapter Type Stand-off adapter

Mounting 3/4 in through hole

**Dimensions** 

Material Thickness 2.591 mm | 0.102 in

Material Specifications

Material Type Stainless steel

Mechanical Specifications

**Maximum Loading** Double stack, 1-5/8 in cable

#### Packaging and Weights

 Height, packed
 12 cm | 4.724 in

 Width, packed
 11 cm | 4.331 in

**Length, packed** 1 cm | 0.394 in

Packaging quantity 10

**Weight, gross** 0.58 kg | 1.279 lb

### Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value



# TTS3-56

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.andrew.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant



#### Included Products

31670-5 – Round Member Adapter for 5–6 in round members

SA-38 – Three-Way Snap-in Stand-off Adapter has two slots for round member attachment and 3/8"

holes for angle adapter integration. It includes three 3/4" holes for Snap-in hangers

UAAI – Universal Angle Adapter Insert



# 31670-5



#### Round Member Adapter for 5–6 in round members

#### **Product Classification**

**Product Type** Banding clamp

Product Brand HELIAX®

Ordering Note ANDREW® standard product (Global)

General Specifications

Adapter Type Round member adapter

**Dimensions** 

Compatible Diameter, maximum152.4 mm | 6 inCompatible Diameter, minimum127 mm | 5 in

Material Thickness 0.711 mm | 0.028 in

Material Specifications

Material Type Stainless steel

Mechanical Specifications

**Maximum Loading** Triple stack, 1-5/8 in cable

#### Packaging and Weights

 Height, packed
 36 cm | 14.173 in

 Width, packed
 27 cm | 10.63 in

 Length, packed
 8 cm | 3.15 in

Packaging quantity 10

**Weight, gross** 0.51 kg | 1.124 lb

ANDREW®
an Amphenol company

# 31670-5

# Regulatory Compliance/Certifications

| Agency        | Classification   |
|---------------|--|
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system |
| REACH-SVHC    | Compliant as per SVHC revision on www.andrew.com/ProductCompliance             |
| ROHS          | Compliant  |
| UK-ROHS       | Compliant  |





Three-Way Snap-in Stand-off Adapter has two slots for round member attachment and 3/8" holes for angle adapter integration. It includes three 3/4" holes for Snap-in hangers

#### **Product Classification**

Product Type Stand-off mount

Product Brand HELIAX®

Ordering Note ANDREW® standard product (Global)

### General Specifications

Adapter Type Stand-off adapter

**Mounting** 3/4 in through hole | 3/8 in through hole | Round member

#### **Dimensions**

 Height
 2.54 mm | 0.1 in

 Outside Width
 41.402 mm | 1.63 in

 Outside Length
 85.852 mm | 3.38 in

 Material Thickness
 2.591 mm | 0.102 in

### Material Specifications

Material Type Stainless steel

#### Mechanical Specifications

**Maximum Loading** Double stack, 1-5/8 in cable

### Packaging and Weights

 Height, packed
 12 cm | 4.724 in

 Width, packed
 11 cm | 4.331 in

 Length, packed
 1 cm | 0.394 in

Packaging quantity 10

ANDREW® an Amphenol company

# SA-38

**Weight, gross** 0.58 kg | 1.279 lb

## Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.andrew.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant



### UAAI



## Universal Angle Adapter Insert

#### **Product Classification**

Product Type Insert
Product Brand HELIAX®

Ordering Note ANDREW® non-standard product

#### General Specifications

Adapter Type Adapter

**Mounting** 3/8 in tapped hole

#### **Dimensions**

Outside Width12.7 mm | 0.5 inOutside Length25.4 mm | 1 inMaterial Thickness12.7 mm | 0.5 in

#### Material Specifications

Material Type Stainless steel

### Mechanical Specifications

**Maximum Loading** Triple stack, 1-5/8 in cable

#### Packaging and Weights

 Height, packed
 4 cm | 1.575 in

 Width, packed
 5 cm | 1.969 in

 Length, packed
 1 cm | 0.394 in

Packaging quantity 10

**Weight, gross** 0.13 kg | 0.287 lb

### Regulatory Compliance/Certifications



# UAAI

#### Agency Classification

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.andrew.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant

