

# UA-3

---



Angle Adapter, universal, snap-in, 3/4 in through hole

## Product Classification

<b>Product Type</b>	Adapter
<b>Product Brand</b>	HELIAX®
<b>Ordering Note</b>	CommScope® standard product (Global)

## General Specifications

<b>Adapter Type</b>	Angle adapter
<b>Mounting</b>	3/4 in through hole

## Dimensions

<b>Inside Width</b>	22.352 mm   0.88 in
<b>Outside Width</b>	57.15 mm   2.25 in
<b>Inside Length</b>	25.4 mm   1 in
<b>Outside Length</b>	50.8 mm   2 in
<b>Material Thickness</b>	2.667 mm   0.105 in

## Material Specifications

<b>Material Type</b>	Stainless steel
----------------------	-----------------

## Mechanical Specifications

<b>Installation Torque, maximum</b>	15 ft lb   20.337 N-m
<b>Installation Torque, minimum</b>	11 ft lb   14.914 N-m
<b>Maximum Loading</b>	Triple stack, 1-5/8 in cable

## Packaging and Weights

<b>Height, packed</b>	25 cm   9.843 in
<b>Width, packed</b>	14 cm   5.512 in
<b>Length, packed</b>	12 cm   4.724 in

# UA-3

---

**Packaging quantity** 10  
**Weight, gross** 2.32 kg | 5.115 lb

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

