


# FD5M-576S00DDB5



FDH5000 cabinet with 576 ports, LC/APC, no splitters, dry dielectric flat ribbon, 100 ft stub, 144F feeder, 288F distribution, pad mount with 8 in riser

## Product Classification

<b>Regional Availability</b>	Latin America   North America
<b>Product Type</b>	Fiber distribution hub
<b>Product Series</b>	FDH 5000

## General Specifications

<b>Access</b>	Front
<b>Cable Type</b>	Pigtails - Ribbon
<b>Color</b>	Putty white
<b>Distribution Cables, quantity</b>	2
<b>Distribution Ports, quantity</b>	576
<b>Fibers per Distribution Cable, quantity</b>	288
<b>Fibers per Feeder Cable, quantity</b>	144
<b>Mounting</b>	Pad
<b>Splitter Slots, quantity</b>	9

## Dimensions

<b>Height</b>	901.7 mm   35.5 in
<b>Width</b>	698.5 mm   27.5 in
<b>Depth</b>	330.2 mm   13 in
<b>Cable Length</b>	30.48 m   100 ft
<b>Enclosure Size</b>	Large

## Material Specifications

<b>Finish</b>	Powder coated
<b>Material Type</b>	Aluminum

# FD5M-576S00DDB5

---

## Environmental Specifications

**Environmental Space** Above ground

## Packaging and Weights

**Packaging quantity** 1

**Packaging Type** Pallet

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Above maximum concentration value
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

