

# F-CLAMP-A-2B



KwikClamp™ Hanger for power & fiber cables, 4.5-9 mm, double stack, round or flat mounting; includes hardware

## Product Classification

Product Type	Hanger kit
Product Brand	KwikClamp™
Ordering Note	ANDREW® standard product in Europe, the Middle East, and Africa   Minimum order quantity (MOQ) is 1 box

## General Specifications

Cables per Hanger	1
Color	Black
Hanger Type	KwikClamp™ hanger
Mounting	3–25 mm angle iron   3–25 mm flat plate   Round Member 8-25 mm

## Dimensions

Maximum Stack Height	2
Height	143 mm   5.63 in
Width	32 mm   1.26 in
Length	46 mm   1.811 in
Compatible Cable Diameter Range	4.5–9 mm
Compatible Diameter, maximum	9 mm   0.354 in
Compatible Diameter, minimum	4.5 mm   0.177 in
Hanger Spacing, maximum	1.83 m   6.004 ft

## Electrical Specifications

Return Loss Effect, maximum	0.1 dB
DTF Effect, maximum	0.1 dB

## Material Specifications

Material Type	EPDM rubber   Engineered plastic   Stainless steel
---------------	--

# F-CLAMP-A-2B

---

## Mechanical Specifications

**Vibration Survival** ≥4 hours at resonant frequency

## Environmental Specifications

**Operating Temperature** -40 °C to +70 °C (-40 °F to +158 °F)

**Corrosion Resistance, minimum with no degradation** ≥500 hours in salt spray chamber

**Environmental Strength Capability** Five times cable weight

**UV Resistance, minimum with no degradation** ≥124 hours exposure in accelerated UV life chamber, testing duration 1344 hrs

## Packaging and Weights

**Height, packed** 15.5 cm | 6.102 in

**Width, packed** 30.5 cm | 12.008 in

**Length, packed** 35.5 cm | 13.976 in

**Included** Hardware

**Packaging quantity** 66

**Weight, gross** 9.2 kg | 20.283 lb

## \* Footnotes

**Maximum Stack Height** Fiber, Hybrid, Power