## F-CLAMP-B-2B



KwikClamp™ Hanger for power & fiber cables, 7-22 mm, double stack, round or flat mounting; includes hardware

#### **Product Classification**

Product TypeHanger kitProduct BrandKwikClamp™

Ordering Note ANDREW® standard product in Europe, the Middle East, and

Africa | Minimum order quantity (MOQ) is 1 box

General Specifications

Cables per Hanger

**Color** Black

**Hanger Type** KwikClamp™ hanger

Mounting 3-25 mm angle iron | 3-25 mm flat plate | Round Member 8-

25 mm

Dimensions

Maximum Stack Height 2

 Height
 162 mm | 6.378 in

 Width
 32 mm | 1.26 in

 Length
 42 mm | 1.654 in

Compatible Cable Diameter Range 7-22 mm

Compatible Diameter, maximum22 mm | 0.866 inCompatible Diameter, minimum7 mm | 0.276 inHanger Spacing, maximum1.83 m | 6.004 ft

**Electrical Specifications** 

Return Loss Effect, maximum0.1 dBDTF Effect, maximum0.1 dB

Material Specifications

Material Type EPDM rubber | Engineered plastic | Stainless steel

ANDREW® an Amphenol company

# F-CLAMP-B-2B

### Mechanical Specifications

**Vibration Survival** ≥4 hours at resonant frequency

#### **Environmental Specifications**

**Operating Temperature**  $-40 \,^{\circ}\text{C}$  to  $+70 \,^{\circ}\text{C}$  ( $-40 \,^{\circ}\text{F}$  to  $+158 \,^{\circ}\text{F}$ )

**Corrosion Resistance, minimum with no degredation** ≥500 hours in salt spray chamber

**Environmental Strength Capability** Five times cable weight

**UV Resistance, minimum with no degradation** ≥124 hours exposure in accelerated UV life chamber, testing

duration 1344 hrs

### Packaging and Weights

 Height, packed
 15.5 cm | 6.102 in

 Width, packed
 30.5 cm | 12.008 in

 Length, packed
 35.5 cm | 13.976 in

**Included** Hardware

Packaging quantity 48

**Weight, gross** 7.2 kg | 15.873 lb

\* Footnotes

Maximum Stack Height Fiber, Hybrid, Power