# F-CLAMP-B2-2B



KwikClamp™ Hanger for power & fiber cables, two 7-22 mm holes (alongside each other), double block; includes hardware

#### **Product Classification**

Product TypeHanger kitProduct BrandKwikClamp™

Ordering Note ANDREW® standard product in Europe, the Middle East, and

Africa | Minimum order quantity (MOQ) is 1 box

General Specifications

Cables per Hanger 2

**Color** Black

**Hanger Type** KwikClamp™ hanger

Mounting 3-25 mm angle iron | 3-25 mm flat plate | Round Member 8-

25 mm

**Dimensions** 

Maximum Stack Height 2

 Height
 167 mm | 6.575 in

 Width
 56 mm | 2.205 in

 Length
 46 mm | 1.811 in

**Compatible Cable Diameter Range** 7-22 mm

Compatible Diameter, maximum22 mm | 0.866 inCompatible Diameter, minimum7 mm | 0.276 inHanger Spacing, maximum1.83 m | 6.004 ft

**Electrical Specifications** 

Return Loss Effect, maximum0.1 dBDTF Effect, maximum0.1 dB

Material Specifications

Material Type Engineered plastic | Stainless steel

ANDREW®
an Amphenol company

# F-CLAMP-B2-2B

### Mechanical Specifications

**Vibration Survival** ≥4 hours at resonant frequency

## **Environmental Specifications**

**Operating Temperature**  $-40 \,^{\circ}\text{C} \text{ to } +70 \,^{\circ}\text{C} \, (-40 \,^{\circ}\text{F to } +158 \,^{\circ}\text{F})$ 

**Corrosion Resistance, minimum with no degredation** ≥500 hours in salt spray chamber

Environmental Strength Capability Five times cable weight

**UV Resistance, minimum with no degradation** ≥124 hours exposure in accelerated UV life chamber, testing

duration 1344 hrs

### Packaging and Weights

 Height, packed
 15.5 cm | 6.102 in

 Width, packed
 30.5 cm | 12.008 in

 Length, packed
 35.5 cm | 13.976 in

**Included** Hardware

Packaging quantity 24

**Weight, gross** 5.3 kg | 11.684 lb

# Regulatory Compliance/Certifications

#### Agency Classification

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.andrew.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant



#### \* Footnotes

Maximum Stack Height Fiber, Hybrid, Power

