

F-CLAMP-C-1B

KwikClamp™ Hanger for power & fiber cables, 22–34 mm, single stack; includes hardware



Product Classification

Product Type	Hanger kit
Product Brand	KwikClamp™
Ordering Note	CommScope® standard product in Europe, the Middle East, and Africa Minimum order quantity (MOQ) is 1 box

General Specifications

Cables per Hanger	1
Color	Black
Hanger Type	KwikClamp™ hanger
Mounting	3–25 mm angle iron 3–25 mm flat plate Round Member 8–25 mm

Dimensions

Maximum Stack Height	1
Height	140 mm 5.512 in
Width	45 mm 1.772 in
Length	44 mm 1.732 in
Compatible Cable Diameter Range	22–34 mm
Compatible Diameter, maximum	34 mm 1.339 in
Compatible Diameter, minimum	22 mm 0.866 in
Hanger Spacing, maximum	1.83 m 6.004 ft

Electrical Specifications

Return Loss Effect, maximum	0.1 dB
DTF Effect, maximum	0.1 dB

F-CLAMP-C-1B

Material Specifications

Material Type Engineered plastic | Stainless steel

Mechanical Specifications

Vibration Survival ≥4 hours at resonant frequency

Environmental Specifications

Operating Temperature -40 °C to +70 °C (-40 °F to +158 °F)

Corrosion Resistance, minimum with no degradation ≥500 hours in salt spray chamber

Environmental Strength Capability Five times cable weight

UV Resistance, minimum with no degradation ≥100 hours exposure in accelerated UV life chamber

Packaging and Weights

Height, packed 15.5 cm | 6.102 in

Width, packed 30.5 cm | 12.008 in

Length, packed 35.5 cm | 13.976 in

Included Hardware

Packaging quantity 54

Weight, gross 6.9 kg | 15.212 lb

* Footnotes

Maximum Stack Height Fiber, Hybrid, Power