


F-CLAMP-C-2B



KwikClamp™ Hanger for power & fiber cables, 22-34 mm, double stack; includes hardware

Product Classification

Product Type	Hanger kit
Product Brand	KwikClamp™
Ordering Note	ANDREW® standard product in Europe, the Middle East, and Africa Minimum order quantity (MOQ) is 1 box

General Specifications

Cables per Hanger	1
Color	Black
Hanger Type	KwikClamp™ hanger
Mounting	3-25 mm angle iron 3-25 mm flat plate Round Member 8-25 mm

Dimensions

Maximum Stack Height	2
Height	192 mm 7.559 in
Width	45 mm 1.772 in
Length	44 mm 1.732 in
Compatible Cable Diameter Range	22-34 mm
Compatible Diameter, maximum	34 mm 1.339 in
Compatible Diameter, minimum	22 mm 0.866 in
Hanger Spacing, maximum	1.83 m 6.004 ft

Electrical Specifications

Return Loss Effect, maximum	0.1 dB
DTF Effect, maximum	0.1 dB

Material Specifications

Material Type	Engineered plastic Stainless steel
---------------	--------------------------------------

F-CLAMP-C-2B

Mechanical Specifications

Vibration Survival ≥4 hours at resonant frequency

Environmental Specifications

Operating Temperature -40 °C to +70 °C (-40 °F to +158 °F)

Corrosion Resistance, minimum with no degradation ≥500 hours in salt spray chamber

Environmental Strength Capability Five times cable weight

UV Resistance, minimum with no degradation ≥100 hours exposure in accelerated UV life chamber

Packaging and Weights

Height, packed 15.5 cm | 6.102 in

Width, packed 30.5 cm | 12.008 in

Length, packed 35.5 cm | 13.976 in

Included Hardware

Packaging quantity 27

Weight, gross 5.6 kg | 12.346 lb

* Footnotes

Maximum Stack Height Fiber, Hybrid, Power