## F-CLAMP-D-2B



KwikClamp™ Hanger for power & fiber cables, 34-46 mm, double stack; includes hardware

#### **Product Classification**

Product TypeHanger kitProduct BrandKwikClamp™

Ordering Note ANDREW® standard product in Europe, the Middle East, and

Africa | Minimum order quantity (MOQ) is 1 box

General Specifications

Cables per Hanger 1

**Color** Black

**Hanger Type** KwikClamp™ hanger

Mounting 3-25 mm angle iron | 3-25 mm flat plate | Round Member 8-

25 mm

**Dimensions** 

Maximum Stack Height 2

 Height
 243 mm | 9.567 in

 Width
 57 mm | 2.244 in

 Length
 45 mm | 1.772 in

**Compatible Cable Diameter Range** 34-46 mm

Compatible Diameter, maximum46 mm | 1.811 inCompatible Diameter, minimum34 mm | 1.339 inHanger Spacing, maximum1.83 m | 6.004 ft

**Electrical Specifications** 

Return Loss Effect, maximum0.1 dBDTF Effect, maximum0.1 dB

Material Specifications

Material Type Engineered plastic | Stainless steel

ANDREW®
an Amphenol company

# F-CLAMP-D-2B

### Mechanical Specifications

**Vibration Survival** ≥4 hours at resonant frequency

### **Environmental Specifications**

Operating Temperature  $-40 \,^{\circ}\text{C}$  to  $+70 \,^{\circ}\text{C}$  ( $-40 \,^{\circ}\text{F}$  to  $+158 \,^{\circ}\text{F}$ )

**Corrosion Resistance, minimum with no degredation** ≥500 hours in salt spray chamber

Environmental Strength Capability Five times cable weight

**UV Resistance, minimum with no degradation** ≥100 hours exposure in accelerated UV life chamber

Packaging and Weights

 Height, packed
 15.5 cm | 6.102 in

 Width, packed
 30.5 cm | 12.008 in

**Length, packed** 35.5 cm | 13.976 in

**Included** Hardware

Packaging quantity 21

**Weight, gross** 5.8 kg | 12.787 lb

\* Footnotes

Maximum Stack Height Fiber, Hybrid, Power