F-CLAMP-E-3B



KwikClamp[™] Hanger for power & fiber cables, 9-12 mm, triple stack; includes hardware

Product Classification

Product Type	Hanger kit
Product Brand	KwikClamp™
Ordering Note	ANDREW® standard product in Europe, the Middle East, and Africa Minimum order quantity (MOQ) is 1 box
General Specifications	
Cables per Hanger	1
Color	Black
Hanger Type	KwikClamp™ hanger
Mounting	3–25 mm angle iron 3–25 mm flat plate Round Member 8- 25 mm

Dimensions

Maximum Stack Height	3
Height	169 mm 6.654 in
Width	32 mm 1.26 in
Length	46 mm 1.811 in
Compatible Cable Diameter Range	9–12 mm
Compatible Diameter, maximum	12 mm 0.472 in
Compatible Diameter, minimum	9 mm 0.354 in
Hanger Spacing, maximum	1.83 m 6.004 ft
Electrical Specifications	
Return Loss Effect, maximum	0.1 dB
DTF Effect, maximum	0.1 dB
Material Specifications	
Material Type	EPDM rubber Engineered plastic Stainless steel

Page 1 of 2



F-CLAMP-E-3B

Mechanical Specifications

Vibration Survival

≥4 hours at resonant frequency

Environmental Specifications

Operating Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Corrosion Resistance, minimum with no degredation	≥500 hours in salt spray chamber
Environmental Strength Capability	Five times cable weight
UV Resistance, minimum with no degradation	\geq 100 hours exposure in accelerated UV life chamber

Packaging and Weights

Height, packed	15.5 cm 6.102 in
Width, packed	30.5 cm 12.008 in
Length, packed	35.5 cm 13.976 in
Included	Hardware
Packaging quantity	54
Weight, gross	9.6 kg 21.164 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.andrew.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant



* Footnotes

Maximum Stack Height Fiber, Hybrid, Power



©2025 ANDREW, an Amphenol company. All rights reserved. Amphenol and ANDREW are registered trademarks of Amphenol and/or its affiliates in the U.S. and other countries. All product names, trademarks and registered trademarks are property of their respective owners. Revised: April 2, 2025

Page 2 of 2