## 1-2105027-1



Fiber Optic Patch Cord, OM3, LC to LC duplex, 1.8 mm LSZH & OFNR, 11 m, aqua

#### **Product Classification**

Regional Availability

Asia | Australia/New Zealand | China | India

Portfolio CommScope®

**Product Type** Fiber patch cord, duplex

Product Series 210

General Specifications

Connector A, quantity 2

Color, boot ABeigeColor, connector ABeige

Connector B, quantity 2

Color, boot BBeigeColor, connector BBeigeInterface, Connector ALC/UPCInterface, Connector BLC/UPC

Jacket Color Aqua

**Polarity** Pairs, flipped

Total Fibers, quantity 2

Dimensions


 Cord Length
 11 m | 36.089 ft

 Diameter Over Jacket
 1.8 mm | 0.071 in

Ordering Tree



## 1-2105027-1



#### Optical Specifications

Fiber Mode Multimode

**Fiber Type** OM3, LazrSPEED®

Insertion Loss, maximum, connector A0.3 dBInsertion Loss, maximum, connector B0.3 dBReturn Loss, minimum, connector A20 dBReturn Loss, minimum, connector B20 dB

#### **Environmental Specifications**

**Environmental Space**Dual Rated LSZH/Riser

**Qualification Standards** IEC 60332-1 | IEC 60332-3 | IEC 60754 | IEC 61034

Packaging and Weights

Packaging quantity

### Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted



# 1-2105027-1



