

Fiber Optic Patch Cord, Duplex, Multimode OM4, LC/UPC to LC/UPC, 3 mm, LSZH/OFNR, aqua, 8 m

#### **Product Classification**

**Regional Availability** Asia | Australia/New Zealand | China | India

LC/UPC

**Portfolio** CommScope®

**Product Type** Fiber patch cord, duplex

**Product Series** 185

## General Specifications

Connector A, quantity 2

Color, boot A Aqua Color, connector A Beige

Connector B, quantity

Color, boot B Aqua Color, connector B Beige

Interface, Connector A LC/UPC Interface, Connector B

**Jacket Color** Aqua

Pairs, flipped **Polarity** 

2 **Total Fibers, quantity** 


Dimensions

**Cord Length** 8 m | 26.247 ft **Diameter Over Jacket** 3 mm | 0.118 in

## Ordering Tree



## 1859793-8



### Mechanical Specifications

Cable Retention Strength, maximum 11.24 lb @ 0  $^{\circ}$ 

#### Optical Specifications

Fiber Mode Multimode

 Fiber Type
 OM4

 Insertion Loss, maximum
 0.3 dB

 Return Loss, minimum
 20 dB

## **Environmental Specifications**

**Operating Temperature**  $-10 \,^{\circ}\text{C}$  to  $+60 \,^{\circ}\text{C}$  (+14  $^{\circ}\text{F}$  to +140  $^{\circ}\text{F}$ )

**Environmental Space** Dual Rated LSZH/Riser

**Qualification Standards** | IEC 60332-1 | IEC 60332-3 | IEC 60754 | IEC 61034

Packaging and Weights

Packaging quantity

Regulatory Compliance/Certifications

Agency Classification

COMMSC PE°

# 1859793-8

CHINA-ROHS Above maximum concentration value

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted

